



MAIN BOARD

Programme selector

Programme selector

LINE

NEUTRAL

Anti-interference filter

USER INTERFACE

SY. OUT

SY. IN

SY. CLOCK

VEE (12V)

IR. OUT

IR. IN

ASY. OUT

ASY. IN

N.C.

FLOW.S

LEVEL.S

NORM./ZOOM

ANALOGIC pressure level

MOTOR over load cut-out

STATOR

STATOR

MOTOR

K3-CW_RL

K4-HF_RL

LINE ON/OFF

MOTOR_TY

REC_TY

DRAIN_TY

MELV_TY

BELL_TY

PNELV_TY

REC_TY_S

DRAIN_TY_S

Wash valve

Prewash valve

Recirculation pump

Door safety interlock

Door closed sensor

Line door sensor

Pressure switch AE-1

Pressure switch AE-2

Pressure switch AE-3

Pressure switch AE-4

Temperature probe

Door locked lamp

Drain pump

Recirculation pump

Wash valve

Prewash valve

Recirculation pump

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump

Door locked lamp

Temperature probe

Drain pump