



Temperature probe

J5-1
J5-2
J5-3
J5-4
J5-5

NEUTRAL
LINE

Anti-interference filter

ASYNCHRONOUS SERIAL INTERFACE

J7-1
J7-2
J7-3
J7-4

Program selector

J8-1
J8-2

LINE ON/OFF

J6-1
J6-2

MAIN V

DOOR_TY
DOOR_TY_S

DOOR_CLOSED_S

DOOR_TY
DOOR_TY_S

DOOR_CLOSED_S

PWELV_TY
WELV_TY
DRAIN_TY
DRAIN_TY_S

J2-1
J2-2
J2-3
J2-4
J2-5
J2-6

L1 S
HV1 S

AT 31 Pressure switch

J3-1
J3-2
J3-3
J3-4
J3-5
J3-6
J3-7

Prewash valve
Wash valve
Drain pump

N (+5V)

MOTOR OVERLOAD CUT-OUT

STATOR STATOR

ROTOR

MOTOR

K1-WHEAT_RL
K2-CW_RL
K3-CW_RL
K4-HF_RL

MOT_TY_S
MOT_TY

LINE ON/OFF

AE
11
12
14

Pressure switch

Door safety interlock

(1 Level)

21 Pressure switch

22
24

Heating element

124 912510c